



LokoStation Off Weighting Conversion Table

Patient Body Weight

LBS	KG	10%		20%		30%		40%		50%		60%		70%		80%	
		Total kg	Per Dial	Total kg	Per Dial	Total kg	Per Dial	Total kg	Per Dial	Total kg	Per Dial	Total kg	Per Dial	Total kg	Per Dial	Total kg	Per Dial
100	45.5			9.1	4.5	13.6	6.8	18.2	9.1	22.7	11.4	27.3	13.6	31.8	15.9	36.4	18.2
110	50.0			10.0	5.0	15.0	7.5	20.0	10.0	25.0	12.5	30.0	15.0	35.0	17.5	40.0	20.0
120	54.5			10.9	5.5	16.4	8.2	21.8	10.9	27.3	13.6	32.7	16.4	38.2	19.1	43.6	21.8
130	59.1			11.8	5.9	17.7	8.9	23.6	11.8	29.5	14.8	35.5	17.7	41.4	20.7	47.3	23.6
140	63.6			12.7	6.4	19.1	9.5	25.5	12.7	31.8	15.9	38.2	19.1	44.5	22.3	50.9	25.5
150	68.2			13.6	6.8	20.5	10.2	27.3	13.6	34.1	17.0	40.9	20.5	47.7	23.9	54.5	27.3
160	72.7			14.5	7.3	21.8	10.9	29.1	14.5	36.4	18.2	43.6	21.8	50.9	25.5	58.2	29.1
170	77.3			15.5	7.7	23.2	11.6	30.9	15.5	38.6	19.3	46.4	23.2	54.1	27.0	61.8	30.9
180	81.8	8.2	4.1	16.4	8.2	24.5	12.3	32.7	16.4	40.9	20.5	49.1	24.5	57.3	28.6	65.5	32.7
190	86.4	8.6	4.3	17.3	8.6	25.9	13.0	34.5	17.3	43.2	21.6	51.8	25.9	60.5	30.2	69.1	34.5
200	90.9	9.1	4.5	18.2	9.1	27.3	13.6	36.4	18.2	45.5	22.7	54.5	27.3	63.6	31.8	72.7	36.4
210	95.5	9.5	4.8	19.1	9.5	28.6	14.3	38.2	19.1	47.7	23.9	57.3	28.6	66.8	33.4		
220	100.0	10.0	5.0	20.0	10.0	30.0	15.0	40.0	20.0	50.0	25.0	60.0	30.0	70.0	35.0		
230	104.5	10.5	5.2	20.9	10.5	31.4	15.7	41.8	20.9	52.3	26.1	62.7	31.4	73.2	36.6		
240	109.1	10.9	5.5	21.8	10.9	32.7	16.4	43.6	21.8	54.5	27.3	65.5	32.7				
250	113.6	11.4	5.7	22.7	11.4	34.1	17.0	45.5	22.7	56.8	28.4	68.2	34.1				
260	118.2	11.8	5.9	23.6	11.8	35.5	17.7	47.3	23.6	59.1	29.5	70.9	35.5				
270	122.7	12.3	6.1	24.5	12.3	36.8	18.4	49.1	24.5	61.4	30.7	73.6	36.8				
280	127.3	12.7	6.4	25.5	12.7	38.2	19.1	50.9	25.5	63.6	31.8						
290	131.8	13.2	6.6	26.4	13.2	39.5	19.8	52.7	26.4	65.9	33.0						
300	136.4	13.6	6.8	27.3	13.6	40.9	20.5	54.5	27.3	68.2	34.1						
310	140.9	14.1	7.0	28.2	14.1	42.3	21.1	56.4	28.2	70.5	35.2						
320	145.5	14.5	7.3	29.1	14.5	43.6	21.8	58.2	29.1	72.7	36.4						
330	150.0	15.0	7.5	30.0	15.0	45.0	22.5	60.0	30.0								
340	154.5	15.5	7.7	30.9	15.5	46.4	23.2	61.8	30.9								
350	159.1	15.9	8.0	31.8	15.9	47.7	23.9	63.6	31.8								

Total kg (both sides) to off-weight the corresponding percentages
 Settings (in kg) for each dial (half of the Total kg)
 Exceeds maximum off-weight amount of 76kg (38kg per side)